



### Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch lever
Device short name	XCRZ
Product compatibility	XCRA XCRB
Movement of operating head	Rotary
Type of operator	Large roller lever thermoplastic
Type of approach	Lateral approach
Positive opening	With

### Complementary

Associated complete product	XCRB12 XCRA51 XCRA55 XCRB15 XCRB52 XCRB11 XCRA15 XCRB51 XCRA11 XCRA12 XCRB55 XCRA52
-----------------------------	--

### Environment

Ambient air temperature for operation	-25...70 °C
---------------------------------------	-------------

### Packing Units

Package 1 Weight	90 g
Package 2 Weight	2.056 kg

**Offer Sustainability**

---

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

---

**Contractual warranty**

---

Warranty	18 months
----------	-----------

---