


Part Number : [528922496](#)

Product Description : 0.50mm Pitch Easy-On FFC/
FPC Connector, Right-Angle, Surface Mount, ZIF,
Bottom Contact Style, Cable Retention Guide, 24
Circuits, Gold (Au) Contact Plating

Series Number : 52892

Status : Obsolete

Product Category : FFC / FPC Connectors



Documents & Resources


[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[SPK-52892-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	FFC / FPC Connectors
Series	52892
Description	0.50mm Pitch Easy-On FFC/FPC Connector, Right-Angle, Surface Mount, ZIF, Bottom Contact Style, Cable Retention Guide, 24 Circuits, Gold (Au) Contact Plating
Comments	Hinge, Cable Guide
Product Name	Easy-On
UPC	822350307932

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

Physical

Actuator Type	Front Flip
Circuits (Loaded)	24
Contact Position	Bottom
Durability (mating cycles max)	20
Mated Height	2.00mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	254.700/mg
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel

PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	Yes
Pitch - Mating Interface	0.50mm
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-30° to +85°C
Wire/Cable Type	FFC/FPC

This document was generated on Nov 08, 2025

Obsolete