# Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# "FIXING SCREW"



AF1VC820



EAN Code: 3389110543667

## Main

Accessory / separate part category	Mounting accessories	
Quantity per set	Set of 10	
Star-delta starter component	1/4 turn sliding clip nuts and corresponding bolts	

# Complementary

Assembly style	For assembly	
Fixing of mechanism	Screws	
	0.000	
Head mounting	M8 x 20	
ISO thread	M8	
Motor power kW	100 kW	
	200 kW	
	185 kW	
	220 kW	
	315 kW	
	250 kW	
	160 kW	
	90 kW	
	280 kW	
	375 kW	
Motor starter type	Star-delta starters	
Mounting support	Notched AM1-EC rail	
Number of devices	8	
Product compatibility	For uprights AM3-EC	
Net weight	0.024 kg	
Wot Worght	0.023 kg	
	0.025 kg	
Shape of screw head	Hexagonal	
Threaded length	20 mm	
Provided equipment	Washer	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.800 cm
Package 1 Width	1.200 cm
Package 1 Length	2.000 cm
Package 1 Weight	14.000 g

Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	2.000 cm
Package 2 Width	5.000 cm
Package 2 Length	13.000 cm
Package 2 Weight	142.000 g
Unit Type of Package 3	CAR
Number of Units in Package 3	680
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	10.062 kg

# **Logistical informations**

Country of origin

# **Contractual warranty**

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

### **Use Better**

Materials and Substances		
Packaging made with recycled cardboard	No	
Packaging without single use plastic	No	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)	

### **Use Again**

○ Repack and remanufacture		
Take-back	No	