

Angle Grinder XGT® 115 mm GA022G

40Vmax • 115 mm • 3 000 – 8 500 min⁻¹

Efficient brushless tool with brake for cutting and grinding

Brushless, slide switch angle grinder with a 115 mm wheel for demanding professional use. Outperforming performance and efficiency similar to corded 1,000 W class grinder. AWS remote vacuum cleaner start function.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	3000 - 8500 min ⁻¹
Spindle Thread	M14
Bore Size (Arbor Diameter)	22,23 mm
Disc Diameter	115 mm
Anti-Restart Function (NVR Switch)	✓
Electronic brake	✓
AWS ready	✓
Sound Power Level (L _{WA})	92 dB(A)
Sound Pressure Level (L _{pA})	84 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	3,0 - 4,5 kg
Product Dimensions (L x W x H):	425 x 130 x 168 mm

User benefits

- Excellent in continuous heavy-duty work
- New tool-less wheel cover allows for fast and easy angle adjustment and installation/removal of wheel cover
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Electric brake for maximum productivity and increased operator safety
- Brushless motor eliminates carbon brushes, enabling the Brushless motor to run cooler and more efficiently for longer life
- Soft grip handle provides increased comfort on the job
- Slide switch with lock-on for continuous use
- Soft start for smooth start-ups
- Anti-restart function minimises accidental start-up
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing