Cables



Characteristics


- Cable with molded plug connection in varying lengths.
- Wire end with wire end ferrules, crimped ferrules, or tin-plated.
- Straight or angled plug.
- For all fan types with flat plug 2.8 / 3.0 x 0.5.

More at www.ebmpapst.com


Part number	Type	L1	Wires	Plug	Wire end	Flat push-on receptacle	Application
9920120000	LZ120	610	0.5 mm²	G	C	2.8 x 0.5	AC
9920120004	LZ120-4	2 000	0.5 mm²	G	A	2.8 x 0.5	AC
9920120005	LZ120-5	380	0.5 mm²	W	B	2.8 x 0.5	DC
9920120006	LZ120-6	610	0.5 mm²	W	B	2.8 x 0.5	DC
9920120010	LZ120-10	2 500	0.5 mm²	G	B	2.8 x 0.5	AC
9920120011	LZ120-11	2 000	0.5 mm²	G	A	2.8 x 0.5	DC
9920120013	LZ120-13	5 000	0.5 mm²	G	B	2.8 x 0.5	AC
9920120016	LZ120-16	800	0.5 mm²	G	B	2.8 x 0.5	AC
9920120017	LZ120-17	3 000	0.5 mm²	G	A	2.8 x 0.5	AC
9920120018	LZ120-18	4 000	0.5 mm²	G	A	2.8 x 0.5	AC
9920126000	LZ126	1 000	0.5 mm²	G	C	2.8 x 0.5	AC
9920127000	LZ127	1 600	0.5 mm²	G	B	2.8 x 0.5	AC
9920130001	LZ130-1	610	0.82 mm²	G	C	2.8 x 0.5	AC*
9920140000	LZ140	610	0.73 mm²	G	B	2.8 x 0.8	AC

Subject to changes. Dimensions in mm.
* UL-approved


Cable — Straight plug (G)




Cable — Angled plug (W)




Wire end ferrules — Wire end A



Tin-plated — Wire end B



Wire end ferrules — Wire end C



Accessories