

Datasheet

6252-0001 Heavy Duty Footswitch 2083265

- Heavy duty die cast aluminium industrial footswitch
- Study durable industrial footswitch
- Stylish ergonomic design
- Yellow guard, Black base
- Back entry PG13.5 & double side entry M20 cable entry
- DPST + DPST staggered double action, snap break & make
- Sealed to IP67
- Electrical Rating: AC-15 6A 230V; DC-13 6A 24V
- Contact Gap: <3mm, suitable for mains
- Operating Temperature: -25C to +60C



Outline Dimensions

