

CONTACTUM



Make the switch

IP66 1 Gang 13A Non Latching Switched RCD Socket

Stock code: 4904SR



Technical

Associated standards:	BS 7288
Ambient operating temperature:	-5 to 40°C (24hour average not exceeding 25°C)
Fault current rating (mA) :	30
Maximum installation altitude :	2000m
Minimum switch contact gap :	3 mm
Rated current:	13A
Rated frequency:	50-60Hz
Rated voltage:	220-250V
Switched poles :	2 pole
Terminal capacity :	3 x 2.5mm 2 x 4.0mm 2 x 6.0mm

General

Face plate finish:	moulded
Insert colour:	white
Rocker finish:	white moulded
Switched:	Yes

Technical: +44 (0) 208 208 7414 Sales: +44 (0) 208 208 7419 E-mail: sales@contactum.co.uk