



ENGLISH

Datasheet

## RS Pro 200 Piece Nylon Hose Clip Kit, 5.6 to 6.8mm & 26.5 to 30.4mm Inside Diameter

RS Stock No: **473-0963**



### Product Details

RS Pro hose clip kit is made of corrosion-resistant nylon 6.6. This kit has o-clips with size ranging from 5.6 to 6.8 mm inside diameter to 26.5 to 30.4 mm inside diameter. It comes in a pack of 200.

### Features and Benefits

- Withstand pressure up to 200psi
- Working temperature -40 to 130°C
- Resistant to most solvents, petroleum products and common chemicals

**Specifications:**

Largest Clip Inside Diameter Maximum	30.4 mm
Largest Clip Inside Diameter Minimum	26.5 mm
Largest Clip Inside Diameter	26.5 to 30.4 mm
Material	Nylon
Number of Pieces	200
Number of Sizes	15
Smallest Clip Inside Diameter Maximum	6.8 mm
Smallest Clip Inside Diameter Minimum	5.6 mm
Smallest Clip Inside Diameter	5.6 to 6.8 mm