


PRODUCT SHEET

192-...A

Mat chrome-plated 45° elbowed nose inner circlips pliers

Pliers for inner circlip.



Normes : DIN 5256, NF E73-130

reference	nozzle diameter mm	mini. Capacity mm	max. capacity mm	L mm	L"	Weight g
192-10A		8	13	139	5	55
192-13A		12	25	140	5	55
192-17A		19	60	180	7	100
192-21A		40	100	225	9	150