

CASES
1200
Case

Save as PDF



Peli protector cases - Watertight protector cases - 1200 case



Interior dimensions:
23.5 x 18.1 x 10.5 cm (9" x 7" x 4")

Watertight, crushproof, and dust proof

- Easy-open, double-step latches
- Open cell core with solid wall design - strong, light weight
- O-ring seal
- Automatic Pressure Equalization Valve
- Stainless steel hardware
- Pick 'N' Pluck™ with convoluted lid foam
- Unconditionally Guaranteed



Black Silver Yellow Orange Desert_tan

Peli protector cases - Watertight protector cases - 1200 case SPECIFICATIONS

Exterior Dimensions (L x W x D)			Interior Dimensions (L x W x D)		
27 x 24.6 x 12.4 cm (11" x 10" x 5")			23.5 x 18.1 x 10.5 cm (9" x 7" x 4")		
Lid Depth	Bottom Depth	Total Depth			
3 cm (1")	7.4 cm (2.93")	10.4 cm (4.11")			
Lid Depth	Bottom Depth	Total Depth			
3 cm (1.18")	7.4 cm (2.93")	10.4 cm (4.11")			
Weight w/Foam	Weight w/o Foam	Buoyancy Max.			
1.3 kg. (2.87 lbs)	1.2kg (2.65 lbs.)	5.45 kg (12.02 lbs.)			
Range Temperature					
-40 / 99° C (-40 / 210° F)					

1200 Case Certificates

- IP67(1 meter submersion for 30 minutes)
- Def Stan 81-41/STANAG 4280

Materials

Body	Latch	Lid O-Ring	Pins
Polypropylene	ABS	PolymerStainless Steel	
Foam	Purge Body	Purge Vent	Purge O-Ring
1.3 lb Polyurethane	ABS	3 Micron Hydrophobic Non- Wbven PET	70 Shore Nitrile

Configuration

Cat. #	Description
1200	Peli protector cases - Watertight protector cases - 1200 case

Peli protector cases - Watertight protector cases - 1200 case Accessories

Cat. #	Description