

Order Code: RTF027



50,000
Hours



5
Years
Warranty



Performance Data	
Input Power (W)	45
Lumens (lm)	8,600
Energy Rating	A+
Rated Life (Hours)	50,000
Colour Temperature (K)	5,000
Beam Angle (°)	360
Warm Up Time	3 seconds

Electrical Data	
Input Voltage (V) ±10%	220-240

Safety Thermal	
Maximum Ambient Temperature (°C)	45
Minimum Ambient Temperature (°C)	-40

Physical Data	
Case Material	Polycarbonate
Dimensions (mm)	305 x 100
Dimensions LxWxH (mm)	305 x 100
Base	E40
IP Rating	IP20

Notes:

Ventures Professional Retrofit range of LED lamps are fully suitable for use within enclosed Luminaires.

These Professional Retrofit lamps must be installed in a manner to allow sufficient free airflow around the lamp and that the lamp ventilation slots are free from obstruction and reasonably protected from dust and debris, enabling the integral cooling fan to work effectively - noting the lamp is thermally protected and will dim to achieve a safe temperature under adverse conditions. This Product Specification contains data about typical performance at nominal power. Actual values may depend on ballast and applications. Complies with (CE), Low Voltage (CE), WEEE and RoHSDirective.

Data is based upon tests performed by Venture Lighting in a controlled environment and is representative of relative performance at the relevant nominal power/voltage (e.g. 110/240/415). Actual performance can vary depending on operating conditions.

Data is subject to change without notice.