

Features

- Conductor Material: *100% copper wires*
- Jacket Material: *PVC, black*
- Cable Length: *5M*
- Easy to install and reliable connection
- Color: *Black*

RS PRO Telephone Cable

RS Stock No.: 0707864



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against

demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This is a RJ10 4P4C to RJ10 4P4C data cable for both data and voice use, overall length is 5M.

Both ends are durable RJ10 4P4C modular connector;

Straight-through pin out for both data and voice use;

100% copper 6 conductors black wire;

Can be used as phone handset or receiver extension cable, data cable, controller cable, digital motor cable.

General Specifications

<i>Number of Strands</i>	<i>4</i>
<i>Conductor Strand Type</i>	<i>Stranded</i>
<i>Terminated/Unterminated</i>	<i>Terminated; Unterminated</i>
<i>Connector Type</i>	<i>Male RJ10</i>
<i>Connector B</i>	<i>Male RJ10</i>
<i>Connector A</i>	<i>Male RJ10</i>
<i>Outer Sheath Material</i>	<i>PVC;</i>
<i>Sheath Colour</i>	<i>Black</i>
<i>Conductor Material</i>	<i>Bare Copper</i>
<i>Drain Wire</i>	<i>No</i>
<i>Fire Behaviour</i>	<i>Flame Retardant.</i>

Mechanical Specifications

<i>Length</i>	<i>5m</i>
<i>Outer Diameter</i>	<i>2.4*4.8mm</i>
<i>Sheath Thickness</i>	<i>0.6mm</i>

<i>Insulator Diameter</i>	0.9mm +/-0.05
<i>American Wire Gauge</i>	28AWG
<i>Cross Sectional Area</i>	0.079mm ²
<i>Size of Strands</i>	7/0.12mm, 28AWG
<i>Core Strands</i>	7/0.12mm

Approvals

<i>Compliance/Certifications</i>	RoHS, Reach
<i>Declarations</i>	RoHS, Reach

