

**8043 Lifting eye nuts, high-tensile alloy steel**

CE

**TECHNICAL DATA**

- safety factor: 4
- heat treatment: hardening and tempering

• traceability code


**LABORATORY TESTS**

- chemical analysis
- metallographic analysis
- tensile test
- fatigue test (20,000 cycles)
- proof load test (100% of batch)

**AVAILABLE CERTIFICATES**

- Technical product specifications
- Test report UNI EN10204 type 2.2
- Inspection certificate UNI EN10204 type 3.1
- CE Declaration of Conformity



		art.	Ø mm	$\frac{A}{2}$ mm	F mm	WLL kg
	080430206	8043 M6	M6	1	20	400
*	080430208	8043 M8	M8	1,25	20	800
*	080430210	8043 M10	M10	1,50	25	1000
*	080430212	8043 M12	M12	1,75	30	1600
	080430214	8043 M14	M14	2	35	3000
	080430217	8043 M16	M16	2	40	4000
	080430218	8043 M18	M18	2,5	40	5000
	080430221	8043 M20	M20	2,5	50	6000
	080430222	8043 M22	M22	2,5	50	7000
	080430225	8043 M24	M24	3	55	8000
	080430227	8043 M27	M27	3	60	10000
*	080430230	8043 M30	M30	3,5	60	12000