



ENGLISH

Datasheet

## RS Pro Stroboscope, Maximum Speed 300000rpm

RS Stock No: **845-9725**



### Product Details

RS Pro stroboscope is a professional and very high performance pocket stroboscope that is capable of 300,000 flashes per minute, high light intensity and excellent IP65 sealing making it among the best performing in its class. Flash frequency, duration of the flash, a delay period and phase shift are just some of its many functions.

### Features and Benefits

- Maximum 300,000 flashes per minute
- Protection class IP65 (splash water and dust)
- Light emission 4800 Lux at 6000 FPM at 30 cm
- Wide range of influencing light emission, frequency and trigger signal
- Heavy duty design with rubber holster

**Specifications:**

Best Accuracy	±0.02%
Dimensions	191 x 82 x 60 mm
Flash Colour	LED White
Height	60 mm
Length	191 mm
Maximum Operating Temperature	+45°C
Maximum Speed	300000 rpm
Minimum Flash Rate	30 fp/min
Minimum Operating Temperature	0°C
Minimum Speed	30 rpm
Weight	400 g
Width	65 mm