

Hot air tool - Professional Line

# PRO HM 2320 ESD

EAN 4007841 091347

Article number 091347



series 5



Timer function

2300 W

2300 W Output

Display

Display (LCD)



80 - 650 °C



stepless adjustable



150 - 500 l/min.



Suitable for  
pluggable nozzles



VDE



CE

## Function description

Precision digital control. Electronically controlled HM 2320 E hot air tool. 2300 W, digital temperature setting by joystick from 80 – 650 °C, temperature indicated in 10 °C steps on LCD display. Airflow regulation in 2 stages of 150 and 500 l/min. ESD-compliant, meets the requirements defined in IEC DIN EN 61340-5-1; part 5-1:2008 ff.

## Technical specifications

|                                            |                           |
|--------------------------------------------|---------------------------|
| Temperature                                | 80 – 650 °C               |
| Airflow rate                               | 150 – 500 l/min           |
| Temperature setting                        | in 10°C steps by joystick |
| Settings made via                          | joystick                  |
| Temperature display                        | LCD display               |
| Airflow control                            | Settings                  |
| Programming function                       | Yes                       |
| Loc function                               | Yes                       |
| Residual heat indicator                    | Yes                       |
| Cool function                              | No                        |
| Motor, type                                | Brush motor               |
| Heating element                            | Ceramic heating element   |
| Mains power supply                         | 230 V / 50 – 60 Hz        |
| Function, hanger                           | Yes                       |
| Function, life expectancy, motor           | 1000 h                    |
| Function, life expectancy, heating element | 600 h                     |

|                             |                   |
|-----------------------------|-------------------|
| Replaceable heating element | No                |
| Restart protection          | No                |
| Temperature scanner         | Yes               |
| Fine dust filter            | No                |
| Thermal cut-out             | Yes               |
| Thermostat                  | Yes               |
| ESD                         | Yes               |
| Nozzle receiver, type       | 34                |
| Cord length                 | 3 m               |
| Dimensions (L x W x H)      | 253 x 87 x 200 mm |
| PU1, net weight             | 1,044 kg          |
| Manufacturer's Warranty     | 1 year            |
| PU1, EAN                    | 4007841091347     |
| Output                      | 2300 W            |
| Product category            | Hot air tool      |

<https://www.steinel.de/en/>

Subject to technical modifications

04.2025 Page 1 from 2

# PRO HM 2320 ESD

EAN 4007841 091347

Article number 091347



## Accessories

|                    |                                                   |
|--------------------|---------------------------------------------------|
| EAN 4007841 074616 | Soldering reflector nozzle 10 mm                  |
| EAN 4007841 034566 | HL Tool Stand                                     |
| EAN 4007841 010294 | Sieve reflector nozzle 50 x 35 mmT421T399:T827    |
| EAN 4007841 009571 | Reduction nozzle                                  |
| EAN 4007841 075569 | 12-piece hot-air accessory kit                    |
| EAN 4007841 070618 | Reduction nozzle                                  |
| EAN 4007841 073114 | Plastic welding rod                               |
| EAN 4007841 006648 | Crimp connectors                                  |
| EAN 4007841 072766 | Shrink tubing III                                 |
| EAN 4007841 006662 | Crimp connectors - Ø 0.1 - 6.0 mm                 |
| EAN 4007841 071318 | Shrink tubing I                                   |
| EAN 4007841 006655 | Crimp connectors                                  |
| EAN 4007841 070717 | Reduction nozzle                                  |
| EAN 4007841 006785 | Pressure roller Silicone Ø 35 mm                  |
| EAN 4007841 074210 | Plastic welding rod                               |
| EAN 4007841 009601 | Flexible hot air tool stand with suction pad foot |
| EAN 4007841 071417 | Shrink tubing II                                  |
| EAN 4007841 070212 | Surface nozzle                                    |
| EAN 4007841 075811 | Shrink tubing kit                                 |
| EAN 4007841 010317 | Paint Scraper Set                                 |
| EAN 4007841 070915 | Welding nozzle                                    |
| EAN 4007841 070113 | Surface nozzle                                    |
| EAN 4007841 070311 | Window nozzle                                     |
| EAN 4007841 014919 | Temperature scanner HL Scan                       |
| EAN 4007841 070519 | Reflector nozzle                                  |
| EAN 4007841 009595 | Flexible hot air tool stand with magnetic foot    |
| EAN 4007841 034122 | Pressure roller 40mm - Teflon                     |
| EAN 4007841 073411 | Plastic welding rod                               |
| EAN 4007841 070410 | Window nozzle                                     |
| EAN 4007841 071219 | Plastic welding rod                               |
| EAN 4007841 093211 | Pressure roller 50mm - Rubber                     |
| EAN 4007841 074715 | Wide-slit nozzle                                  |
| EAN 4007841 078218 | Fine dust filter HL 1920 E - HG 2320 E            |
| EAN 4007841 053963 | Hot Air Tool Guard Cage HL 1820 S - HG 2320 E     |