

## FEATURES

- Durable and lightweight
- Corrosion resistant
- Resistant to greases and oils
- Good electrical and thermal insulating properties
- Resistant to a wide range of temperatures

## RS PRO, M4 Cheese Head, 12mm Nylon Slot Plain

RS Stock No.: 527-684



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

From RS PRO a high-quality machine screw with a slotted Cheese type head for easy tightening with a flat blade screwdriver. This machine screw has a metric thread and is made from high-quality nylon making it strong, lightweight and resistant to corrosion. Nylon also has excellent electrical insulation properties making this machine screw ideal for use in electronics applications.

### General Specifications

<b>Head Shape</b>	Cheese
<b>Drive Type</b>	Slot
<b>Applications</b>	Washing machines, Household appliances, Handheld devices, Electronics and circuit boards, Commercial machinery, Automotive parts

### Mechanical Specifications

<b>Thread Size (Metric)</b>	M4
<b>Length Metric</b>	12mm
<b>Material</b>	Nylon
<b>Finish</b>	Plain
<b>Thread Pitch</b>	0.7mm



RS Stock No.	Thread Size	Length (L) (mm)
<a href="#">527-656</a>	M3 x 0.50	20
<a href="#">527-684</a>	M4 x 0.70	12
<a href="#">527-690</a>	M4 x 0.70	16
<a href="#">527-707</a>	M4 x 0.70	20
<a href="#">527-735</a>	M5 x 0.80	12
<a href="#">527-779</a>	M6 x 1.00	12
<a href="#">527-785</a>	M6 x 1.00	16
<a href="#">527-791</a>	M6 x 1.00	20
<a href="#">527-808</a>	M6 x 1.00	25
<a href="#">527-814</a>	M6 x 1.00	30
<a href="#">527-971</a>	M3 x 0.50	6
<a href="#">527-987</a>	M3 x 0.50	12
<a href="#">527-993</a>	M3 x 0.50	16

