


FEATURES

- **3 in 1 Dimming:** Offers flexibility with 0/1-10 V dc, PWM signal, and resistance dimming options
- **16.67 A Driver Current:** Supports high power LED systems
- **200-240 V AC Input Voltage:** Compatible with standard AC power supplies
- **IP66 Rating:** Provides excellent protection against dust and water
- **Constant Voltage Operation:** Ensures stable and consistent lighting output
- **Single Output:** Simplifies installation and reduces wiring complexity

RS PRO 200W LED Driver, IP66 12V Output

RS Stock No: 642-776



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO LED Driver is designed to provide a reliable power source for LED lighting systems. With a maximum output power of 200W and an output voltage of 12V, it ensures efficient operation for various lighting applications. The IP66 rating makes it suitable for use in challenging environments, offering protection against dust and water ingress.

General Specifications

Dimming Operation	3 in 1 Dimming, 0/1-10 V dc, PWM Signal, Resistance
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver

Electrical Specifications

Driver Current	16.67 A
Input Voltage	200-240 V ac
Input Voltage Type	AC
Maximum Output Power	200 W
Output Voltage	12 V

Protection Category

IP Rating	IP66
-----------	------

Approvals

Standards/Approvals	CE, EN55015, EN61000-3-2, EN61000-4-2,3,4,5,6,11, EN61347-1, EN61347-2-13, EN61547
---------------------	--