

B1005 - K-Jump/ K-Trek/ K-Rush S1P HRO SRC

Collection: Kaptiv

Upper: Breathable Fabric

Lining: SmellStop Antiodor and Antibacterial*

Midsole: Fresh'n Flex

Toecap: Aluminium

Sole: Double-Density PU/HRO Rubber i-daptive® Technology

Outer Carton: 10

Kaptiv

The first safety footwear range with stability control, designed to offer incredible dynamic comfort.



Standards

UNI EN ISO 20345:2012 S1P (HRO SRC)

Features

- Anti-static footwear
- 200 joules resistant toe-cap
- Puncture resistant sole
- Shock absorption in the heel region
- Heat resistant 1 minute up to 300°C
- Hydrocarbons resistant
- Men's width
- Women's width
- Orthopaedic made to measure footbed, complying with european norms DGUV112-191

B1005 - K-Jump/ K-Trek/ K-Rush S1P HRO SRC

Commodity Code: 6404199000

Test House

A.N.C.I. Servizi S.R.L (CIMAC) (Notified Body No.: NB: 0465)
Via Alberto Riva Villasanta, 3
, Italy
Cert No: F-113-00280-18 rev.01

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
B1005BKB36	Black/Blue	67.0	41.0	36.0	1.1200	0.0989	8054633495063	
B1005BKB37	Black/Blue	67.0	41.0	36.0	1.2070	0.0989	8054633495070	
B1005BKB38	Black/Blue	67.0	41.0	36.0	1.2700	0.0989	8054633495087	
B1005BKB39	Black/Blue	67.0	41.0	36.0	1.3000	0.0989	8054633493588	
B1005BKB40	Black/Blue	67.0	41.0	36.0	1.3200	0.0989	8054633493595	
B1005BKB41	Black/Blue	67.0	41.0	36.0	1.3900	0.0989	8054633493601	
B1005BKB42	Black/Blue	67.0	41.0	36.0	1.4200	0.0989	8054633493618	
B1005BKB43	Black/Blue	67.0	41.0	36.0	1.4600	0.0989	8054633493625	
B1005BKB44	Black/Blue	67.0	41.0	36.0	1.5300	0.0989	8054633493632	
B1005BKB45	Black/Blue	67.0	41.0	36.0	1.5900	0.0989	8054633493649	
B1005BKB46	Black/Blue	67.0	41.0	36.0	1.6500	0.0989	8054633493656	
B1005BKB47	Black/Blue	67.0	41.0	36.0	1.6440	0.0989	8054633493663	
B1005BKB48	Black/Blue	67.0	41.0	36.0	1.7100	0.0989	8054633493670	