


Deep groove ball bearings, single row, seal on both sides

Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
15	35	11	8,06	3,75	0,16	-	13000	0,045	6202-2RSH *



Calculation factors

$k_r = 0,025$

$f_0 = 13$