

Datasheet

RS PRO Tungsten Carbide Burrs

Stock No: 1947978



B

Shape B, cylinder with end tothing
 Diamond Cut: Universal cutting style.
 Fast material removal.
 Smooth finish.
 Granular chip break.

Technical Information

- high-performance tungsten carbide
- with cross tothing





Application

To deburr, break edges, trim, process welding seams and surface processing

Fields of application

For high-alloy steels, non-rusting steels, acid-resistant steels, heat-resistant steels, die-casts and plastics

Technical Specifications:

RS No.	Burr Shape	Burr Pattern	 Burr Diameter	 Burr Length	 Shank Length	 Shank Diameter
1947978	Cylinder with end cut	Diamond	12	25	65	6