

Angle Grinder XGT® 115 mm

GA012G

40V max • 115 mm • 8 500 min⁻¹

Efficient brushless tool with paddle switch for cutting and grinding

A compact, brushless angle grinder with paddle switch and 115 mm blade diameter for demanding professional use. The machine features standard electronics, electronic brake, overload protection and AFT-active feedback detection technology.



Technical specifications

No load speed	8500 min ⁻¹
Max. Depth of Cut	29 mm
Spindle Thread	M14
Disc Diameter	115 mm
Anti-Restart Function (NVR Switch)	✓
Dead Man's Switch (No Lock-On)	✓
Sound Power Level (L _{WA})	92 dB(A)
Sound Pressure Level (L _{pA})	84 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Product Dimensions (L x W x H):	410 x 130 x 168 mm
Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Bore Size (Arbor Diameter)	22,23 mm

User benefits

- Excellent in continuous heavy-duty work
- New tool-less wheel cover allows for fast and easy angle adjustment and installation/removal of wheel cover
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Electric brake for maximum productivity and increased operator safety
- Brushless motor eliminates carbon brushes, enabling the Brushless motor to run cooler and more efficiently for longer life
- Soft grip handle provides increased comfort on the job
- Anti-restart function minimises accidental start-up
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Side grip can be positioned on both sides for operator convenience
- Spindle lock for easy wheel changes
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing