

BIZ1 - Bizweld Work FR Coverall

Collection: Bizweld™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizweld Work: 100% Cotton, 330g

Outer Carton: 12

Product information

Voted the number one favourite coverall in the welding industry, our best selling Bizweld coverall is ideal for offering complete protection to workers exposed to heat. The generous fit provides comfort and allows the wearer to work unhindered whilst ample storage space, rule pocket and concealed mobile phone pocket hold equipment securely and safely.

Bizweld™ Work

Bizweld™ Work protective clothing have been specially designed to guarantee comfort, performance and safety whilst providing effective function at all times. Bizweld™ Work has been rigorously tested to ensure total compliance with the latest international standards.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 1 (A1+A2)

IEC 61482-2 IEC 61482-1-1 (ELIM 8.3 CAL/CM², ATPV 10.9 CAL/CM²)

ASTM F1959/F1959M-12 (ATPV 11.2 CAL/CM² (HAF = 80.4%))



Features

- Protection against radiant, convective and contact heat
- Certified protection against molten metal splash
- Concealed stud front for easy access
- Chest pockets with stud closure
- Stud adjustable cuffs for a secure fit
- Rule pocket
- Radio loop for easy clipping of a radio
- Concealed phone pocket
- 6 pockets for ample storage
- CE-CAT III
- CE certified

BIZ1 - Bizweld Work FR Coverall

Commodity Code: 6211321000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

Cert No: 2777/12872-03/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
BIZ1NARXS	Navy	43.0	28.0	52.0	1.1940	0.0626	5036108187690	25036108674392
BIZ1NARS	Navy	43.0	28.0	52.0	1.2140	0.0626	5036108039241	25036108607260
BIZ1NARM	Navy	43.0	28.0	52.0	1.2430	0.0626	5036108039258	25036108607253
BIZ1NARL	Navy	43.0	28.0	58.0	1.3380	0.0698	5036108039265	25036108607246
BIZ1NARXL	Navy	43.0	28.0	58.0	1.3920	0.0698	5036108039272	25036108607277
BIZ1NARXXL	Navy	43.0	28.0	58.0	1.4030	0.0698	5036108039289	25036108607284
BIZ1NARXXXL	Navy	43.0	28.0	58.0	1.4740	0.0698	5036108039296	25036108607291
BIZ1NAR4XL	Navy	43.0	28.0	58.0	1.4870	0.0698	5036108039302	25036108607222
BIZ1NAR5XL	Navy	43.0	28.0	58.0	1.5100	0.0698	5036108141999	25036108607239
BIZ1NAR6XL	Navy	43.0	28.0	58.0	1.6010	0.0698	5036108215805	25036108702507