

BUMPER

Features

- **Door Stops** – Prevents overextension and protects surrounding surfaces
- **Spacers**– Ensure accurate positioning in various setups
- **Vibration Damping** – Minimizes noise and mechanical vibrations


Conical Bumper Stop 85D x 52H

SKU.: 0734065



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

BUMPER



Bumper Dimensions

Diameter (mm)	85
Height (mm)	52

BUMPER

Product Description

Crafted from a high-quality blend of Styrene-Butadiene Rubber (SBR) and Natural Rubber (NR), our premium rubber bumpers are built to deliver long-lasting durability, flexibility, and impact resistance. Designed for both residential and industrial use, these bumpers are available in two convenient sizes to suit a variety of applications.

Each unit features a pre-drilled, countersunk hole for quick and secure installation using an M10 fixing bolt (sold separately). Whether you're looking to prevent door slams, reduce vibration, or protect surfaces from repeated impact, these rubber stoppers offer a reliable and practical solution.

With a sleek black finish, they blend seamlessly into any environment while providing robust protection and support.

General Specifications

Material	NR/SBR
Colour	Black

Mechanical Specifications

Weight	0.27KG
Tensile Strength	4Mpa
Elongation	200%
Hardness	75ShA

Operation Environment Specifications

Maximum Temperature	70°C
Minimum Temperature	-15°C