

## Han 10B-Metallkappe



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 010 5404
Specification	Han 10B-Metallkappe
HARTING eCatalogue	<a href="https://harting.com/09300105404">https://harting.com/09300105404</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> B
Type of accessory	Protection cover
Description of the accessory	for bearing pedestal

### Version

Size	10 B
Locking type	Single locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Metal
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes



**Pushing Performance**  
Since 1945

## Material properties

California Proposition 65 substances	Nickel
--------------------------------------	--------

## Commercial data

Packaging size	1
Net weight	59.9 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140045279
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467