



Application Range

Robust watertight cable gland with conical sealing element for pumps and floater switches.

Technical Data

Material: Body: Nickel Plated Brass
 Seal: CR/NBR
 O Ring: NBR
 Locknut: Nickel Plated Brass

Protection Rating: IP68 – 10Bar

Temperature Range: -20°C to +80°C

Article List

RS Part Number	Manufacturers Part Number	Thread Size	Clamping Range (mm)	Spanner Wrench (mm)	Overall Length (mm)	Thread Length (mm)
390-044	59000121 + 52103020	M20	5 – 6.8	22	26.5	13
390-050	59000141 + 52103020	M20	6.8 – 8.8	22	26.5	13
390-066	59000151 + 52103020	M20	8.5 – 10.8	22	26.5	13
390-072	59000171 + 52103020	M20	10.8 – 12.8	22	26.5	13