



Housing units GLCTE20-XL (Series GLCTE)

two-bolt flanged housing units, cast iron, eccentric locking collar, P seals

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	20 mm
H	90,5 mm
U	33 mm
A ₁	17 mm
A ₂	9,5 mm
B ₁	31 mm
d _{3 max}	33 mm
J	71,4 mm
L	66,5 mm
N	9 mm
Q	M6 Lubrication hole 45°

m	0,39 kg	Mass
C _r	13600 N	Basic dynamic load rating, radial
C _{0r}	6600 N	Basic static load rating, radial
	GLCTE04	Designation of housing
	GRAE20-XL-NPP-B	Designation of bearing



