

## Datasheet

# RS Pro Stainless Steel Bolt Anchor M12, fixing hole diameter 12mm, length 95mm

RS Stock No: **622-1994**



## Product Details

RS Pro captive stud bolt anchor made of A4-316 grade stainless steel resist corrosion. This bolt anchor is suitable for use in concrete with a compressive strength greater than 20 N/mm<sup>2</sup>. The bolt anchor measures 95 mm long with M12 threading that is suitable for 12 mm fixing hole diameter.

## Features and Benefits

- Captive stud through bolt anchor
- A4-316 grade stainless steel construction
- Suitable for use in concrete over 20N/mm<sup>2</sup>
- Fixing hole diameter of 12 mm
- 95 mm long



**Specifications:**

Material	Stainless Steel
Type	Captive Stud Through Bolt Anchor
Fixing Hole Diameter	12 mm
Length	95 mm
Maximum Fixing Thickness	10 mm
Thread Size	M12
Grade	316 (A4)
Minimum Hole Depth	80 mm