

1-1871058-4 ✓ ACTIVE



TE Internal #: 1-1871058-4

Board-to-Board, 164 Position, 1 mm [.039 in] Centerline, Vertical, Black, 11 mm [.433 in] Height, 8.88 mm [.35 in] Width, PCI & PCI Express Connectors

[View on TE.com >](#)

Connectors > PCB Connectors > Card Edge Connectors > PCI & PCI Express Connectors



Connector System: **Board-to-Board**

Number of Positions: **164**

PCI Generation: **2**

Centerline (Pitch): **1 mm [.039 in]**

Termination Post & Tail Length: **3.25 mm [.128 in]**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board

Configuration Features

Number of PCB Mount Retention Features	2
Number of Positions	164
PCB Mount Orientation	Vertical
Ejector	Without

Electrical Characteristics

Operating Voltage	50 VAC
-------------------	--------

Body Features

Product Weight	2.863 g
Primary Product Color	Black

Contact Features

Contact Current Rating (Max)	1.1 A
------------------------------	-------



PCB Contact Termination Area Plating Material Thickness	.5 μ m
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	.76 μ m[30 μ in]

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	3.25 mm[.128 in]

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Housing Material	High Temperature Thermoplastic
Centerline (Pitch)	1 mm[.039 in]

Dimensions

PCB Thickness (Accepted)	1.57 mm[.062 in]
Connector Length	89 mm[3.504 in]
Connector Height	11 mm[.433 in]
Connector Width	8.88 mm[.35 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Bus Type	PCI Express
PCI Generation	2

Packaging Features

Packaging Method	Box & Tray, Tray
Packaging Quantity	30

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-2337939-4
PCIE GEN4 CON,SMT,164POS,30u", MYLAR,HT



TE Part # 1734774-1
PCI EXP 3.1L 36 POS WHT G/F



TE Part # 1871058-1
PCI EXPRESS CONN. EON TYPE, 36P, L=2.0

Customers Also Bought



TE Part #5-103957-4
4X5 MTE RCPT SR LATCH .100CL



TE Part #4-175643-2
1.25FP,P12,DL,B,N,TU,5.00,6.90



TE Part #350543-1
04P CMNL HDR ASSY SHORT NATL



TE Part #963120-1
8P JUNIOR TIMER HOUSING



Documents

Product Drawings

PCI EXPRESS CONN. EON TYPE, 16

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-1871058-4_E.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1871058-4_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1871058-4_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

Japanese