

1670A
flanged precision squares made from ground steel

	art.	L mm	L1 mm	B mm	C mm	H mm	S mm	g
016700110	1670A 100	100	70	19,5	5,6	19,5	5,2	180
016700115	1670A 150	150	100	19,5	5,6	19,5	5,2	265
016700120	1670A 200	200	130	19,5	5,6	19,5	5,2	355
016700125	1670A 250	250	165	24,0	5,6	24,0	5,3	550
016700130	1670A 300	300	175	29,0	5,6	29,0	5,2	735
016700140	1670A 400	400	230	29,3	5,5	29,3	5,3	1015
016700150	1670A 500	500	280	29,3	5,5	29,3	5,3	1200
016700160	1670A 600	600	330	29,5	5,5	29,5	5,3	1400
016700180	1670A 800	800	420	39,0	6,6	39,0	6,3	3085
016700199	1670A 1000	1000	500	39,0	6,7	39,0	6,5	4000

