



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

TE Part #320677
BUDGET R 22-16COMM 22-18MIL 2

TE Part #41616
250 FASTON TAB BR

TE Part #245582-001
T42-100FR

TE Part #6450551-1
MBXL VERT RCPT 24S+6P



TE Part #790319-3
250 PL MKI REC. 12-10AWG PTBR



TE Part #1969803-1
03P UMNL PIN HDR ASSY NATL, PIN V0 GW



TE Part #350923-3
UMNL SOK 10-12 .0125 PTPPHBZ



TE Part #820059-000
301A022-25-0



TE Part #CSI-UFFR-100-UFFR
U.FL/MHF1 to U.FL/MHF1 100mm 1.13 OD



TE Part #5227169-8
BNC - SOLDER RECEPT

Documents

Product Drawings

CHAMP.050 REC ASS'Y 26P PB-FREE

English

CAD Files

Customer View Model

ENG_CVM_CVM_5178238-4_O.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5178238-4_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5178238-4_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

CHAMP.050 Series(II) Connector Wire to Board Type

English

Product Specification

English

Product Specification

English