



Visit the website for your country to get more information and discover our products.

India ▾

[Proceed](#)

HellermannTyton

09/07/2026

Thermal transfer printer including software, desktop, 300dpi, grey

Art.-No. 556-00457 | TT431SB-PL-GY | [Copy item description](#)



- Set consisting of thermal transfer printer and TagPrint Pro software
- Small to medium volume single sided printing
- Print on HellermannTyton cable markers and labels
- Uses standard ribbons
- Barcodes: standard and 2D
- Print speed up to 150 mm/s
- Adjustable label sensor
- Multiple language selection
-

[Show more](#) ▾





Visit the website for your country to get more information and discover our products.

[Proceed](#)

HellermannTyton

09/07/2026

Thermal transfer printer incl. software

Base Data

Application	The TT431 thermal transfer printer is perfect for printing on HellermannTyton materials such as self-adhesive labels, shrinkable tubing and identification tags. Thanks to its low weight and compact construction, the TT431 integrates seamlessly into any workstation. It is easy to use due to its intuitive colour LCD touch display and clear status messages which can be shown in multiple languages. The optional cutter and perforator make this printer ideal for a wide range of applications. 300 dpi resolution ensures that barcodes, warning symbols, logos and text are as sharp as they can be.
Colour	Grey (GY)
Material	Plastic (PL)
PART DESCRIPTION	TT431SB-PL-GY
N	
Package Content	1 Set
Package Content packed in	carton
Print Method	thermal transfer print
Print resolution DPI	300 dpi
Product Family	TT431, Small to medium volume printing
Product Group	Thermal transfer printer incl. software
Short Description	Thermal Transfer Printer 300 dpi
Type	TT431SB
Weight/Unit	5.0 kg

Visit the website for your country to get more information and discover our products.

Proceed



09/07/2026

Label Width max (imperial)	
Label Width Min (imperial)	
Label Width min - max	
Length (L)	322 mm
Print Material Height Max (metric)	4000 mm
Print Material Height Min (metric)	5.00 mm
Print Material Width Max (metric)	105.7 mm
Print Material Width Min (metric)	10.00 mm
Width (W)	253 mm



Visit the website for your country to get more information and discover our products.

Proceed

HellermannTyton

09/07/2026

Hazardous Goods	No
Interfaces	USB 2.0, Ethernet 10/100 Base T, RS232
Max. Print Width	105.70 mm
Print Head Type	300 dpi, flat type
Print Speed	up to 150 mm/s
Printer Memory	256 MB RAM
ROHS compliant	Yes
Specifications	 
Supported Barcodes	Standard and 2D
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	No
UL Recognized (US)	No
UL-File Number	E311215



Visit the website for your country to get more information and discover our products.

Proceed

HellermannTyton

09/07/2026

Dimensions: L x W x H (mm) x D

GTIN-13 / EAN 4031026480503

Packaging 1 - Height (m) 0.335 m

Packaging 1 - Length (m) 0.38 m

Packaging 1 - Qty 1

Packaging 1 - Type pcs.

Packaging 1 - Volume (m³) 0.049647 m³

Packaging 1 - Weight (kg) 5.5 kg

Packaging 1 - Width (m) 0.39 m

Packaging 3 - Height (m) 0.335 m

Packaging 3 - Length (m) 0.38 m

Packaging 3 - Qty 1

Packaging 3 - Type carton

Packaging 3 - Volume (m³) 0.0496 m³

Packaging 3 - Weight (kg) 6.0 kg

Packaging 3 - Width (m) 0.39 m

Packaging 4 - Height (m) 1.15 m

Packaging 4 - Length (m) 1.2 m

Packaging 4 - Qty 18

 Visit the website for your country to get more information and discover our products.

[Proceed](#)

HellermannTyton

09/07/2026

g m (kg)

Packaging 4 - Widht 0.8 m
h (m)

More Information

ETIM 7.0 Key	EC001672
ETIM 8.0 Key	EC001672
ETIM 9.0 Key	EC001684
UNSPSC Key	39131505
Variant	desktop

HellermannTyton

 **International**

Imprint

Policy and Values

Sitemap

Data Protection

Contact

Terms of Service

Guidelines and Commitments



Visit the website for your country to get more information
and discover our products.

[Proceed](#)

HellermannTyton

09/07/2026
