

Product information

10.8V RECIPROCATING SAW



JR100DZ

Battery Quantity (1.3Ah)	2
Battery Type	Li-ion
Body only machine	1
Capacity in Wood	50 mm
Capacity in Mild Steel Pipe	50 mm
Stroke Length	13 mm
No Load Speed	0 - 3300 spm
Variable Speed	Either Trigger
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Wood	9.5 m/sec ²
Vibration: Cutting Chipboard	9.5 m/sec ²



- Tool less blade clamp for reciprocating saw blade. Simply turn to remove the blade.
- Rubberised soft grip with non-slip elastomer grip for more control and comfort.
- Single LED job light with pre-glow function.
- Lithium-ion battery, lighter weight, quicker charging and with more run time than an equal voltage Ni-Cad or Ni-MH battery.
- Two switch levers with variable speed control; Trigger switch on tool handle & Paddle switch on tool body to make operation easier at any grip position for versatile applications by using either trigger.
- Lightweight at only 1.2kg.

Details correct as of: 17-6-2014

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makitauk.com