

rotronic

Datenblatt - Fiche technique - Data sheet

11.04.5513




ROLINE GOLD Monitorkabel DVI, ST-ST, (24+1) dual link, 3,0m

**ROLINE Câble pour écran DVI GOLD, M-M, (24+1) dual link,
3,0m**

**ROLINE Gold Monitor Cable, DVI M – DVI M, (24+1) dual link,
3 m**

ROHS-COMPLIANT

LTR	REV.	REMARK
		Page 1 of 2





























NOTE:

- 1.CABLE: [28AWG(7/0.127 T.C)×1P+DRAIN WIRE+AL/MYLAR+MYLAR]×7C+28AWG(7/0.127 T.C)×1P+28AWG(7/0.127 T.C)×3C+AL/MYLAR+DRAIN WIRE(7/0.127 T.C)+BRAID SHIELDS (85%)
JACKET:PVC OD: 8.6±0.15mm, COLOR:BLACK(NK-K01) UL20276 APPROVED,(C20276324-1)
- 2.CONNECTOR:
P1&P2:DVI 24+1 MALE, GOLD FLASH CONTACT,
- 3.SHIELD: GOLD PLATED SHELL.
P1&P2:COPPER FOIL 360° SOLDER TO CONNECTOR SHELL & CABLE BRAID
- 4.HOOD: P1&P2: ASS'Y TYPE, ALUMINUM HOOD GOLD PLATED.
SR: MOLDED TYPE, PVC 30P, COLOR:BLACK(NK-K01).
- 5.TEST REQUEST:
(1) 100% SHORT OPEN & MIS WIRE TEST.
(2) CONTACT RESISITANCE 3 OHMS MAX.
(3) INSULATION RESISITANCE 10M OHMS MIN.
- 6.PACKING: EACH PC / POLYBAG+BIG HEADER CARD+BAR CODE LABEL.

Tolerance Inch M/M		
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05
Draw FANNIE 12/10/10'		
Check		
Engr		

Rotronic co., LTD.			
Title ROLINE Gold DVI Cable, Dual Link, M/M			
Customer P/N: 11.04.5512 / 11.04.5513 / 11.04.5514			
App'd		Customer:	
Scale	NONE	Units	m/m
Dwg No.		REV:A	
200-1469		Sheet 1/2	

WIRE CONNECTION

P1	WIRE COLOR	P2
1		1
2		2
3		3
3		3
4		4
5		5
6		6
7		7
9		9
10		10
11		11
11		11
12		12
13		13
14		14
15		15
16		16
17		17
18		18
19		19
19		19
20		20
21		21
22		22
23		23
24		24
SHELL	BRAID SHIELDS	SHELL

LTR	REV.		REMARK
			Page 2 of 2

200-1469-3	11.04.5514-10	5000±50	10	20
200-1469-2	11.04.5513-10	3000±30	10	20
200-1469-1	11.04.5512-10	2000±30	10	20
DWG	P/N	L±T(mm)	PCS/INNER CARTON	PCS/CARTON

Tolerance Inch M/M			Rotronic co., LTD.			
.X	.015	.30	Title ROLINE Gold DVI Cable, Dual Link, M-M Customer P/N: 11.04.5512 / 11.04.5513 / 11.04.5514 App'd _____ Customer: _____ Scale NONE Units m/m Third Angle Projection 			
.XX	.010	.10				
.XXX	.005	.05				
Draw FANNIE 12/10/10'			Dwg No. 200-1469			
Check			REV: A		Sheet 2/2	
Engr						