



## **Datasheet**

## RS PRO 19mm Metal Pushbutton Switches 24V, Red LED



RS Article No.	Body type	Button type	Contact Configuration	Operating type	Light type	LED color	LED voltage	Terminal Plating
111-5818	Stainless	Flat	1NO 1NC	Lock	Power Logo	white	110V	Silver
111-5829	Stainless	Flat	1NO 1NC	Lock	Power Logo	white	220V	Silver
111-3901	Stainless	Flat	1NO 1NC	Lock	Power Logo	white	24V	Silver











## **SPECIFICATIONS:**

Rating: Ith 5A/250VAC resistive load 3A/250VAC

Contact Resistance: 50mΩ max. @1A 12VDC (initial value)

Insulation Resistance:  $1,000m\Omega$  min. at 500VDC Dielectric Strength: 2,000V RMS @sea level

Operation Temperature: -20°C to 55°C

**Mechanical Life:** 1,000,000 cycles; self-lock 500,000 cycles. **Electrical Life:** 50,000 make-and-break cycles at full load

Torque: 5~14Nm

Panel Thickness: 10mm (Ø19.20mm)

Operation Pressure: 1Pole 2.5±1N / 2Poles 3.5±1N

Travel: about 3.2mm

Ingress Protection: IP67, IK10

## **Materials**

**Bushing: Stainless Steel/ Nickel plated brass/ Aluminum alloy** 

Base: PBT (UL 94-V0), PC (UL 94-V2)

Actuator: PC (UL94-V2); Stainless Steel/ Nickel plated brass/ Aluminum alloy

Inner Assembly: POM/PA66

**SPRING: Spring steel** 

Sealing: Silicone O-Ring: Silicone

Terminal/ Contact: Cooper, Silver plated

**Hex Nut: Nickel plated brass**