

## Han 24B Ex-HBM-Double Lever



Image is for illustration purposes only. Please refer to product description.

Part number	09 36 024 1301
Specification	Han 24B Ex-HBM-Double Lever
HARTING eCatalogue	<a href="https://harting.com/09360241301">https://harting.com/09360241301</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han <sup>®</sup> Ex
Type of hood/housing	Bulkhead mounted housing

### Version

Size	24 B
Locking type	Double locking lever
Field of application	Connectors for explosion hazardous environments
Details	Simple Apparatus for intrinsically safe circuits
Details	ATTENTION! Only to be used with Han <sup>®</sup> Ex inserts!

### Technical characteristics

Tightening torque	1 Nm Fixing screws M4
Limiting temperature	-20 ... +85 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Ambient temperature	-20 ... +40 °C Up to +70 °C in T4
Degree of protection acc. to IEC 60529	IP65 With cable gland

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 5015 (sky blue)
Material (seal)	NBR



**Pushing Performance**  
Since 1945

## Material properties

Material (locking)	Stainless steel
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Commercial data

Packaging size	1
Net weight	307.25 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140054967
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466