

PATO 2/15


Order No.: 1013122

The figure shows a similar product



Conductor marker carrier, open, 15 mm wide, conductor diameter 2.8 - 5.0 mm

Commercial data

EAN	 4 017918 013547
Pack	1000
Customs tariff	39269098
Country of Origin	IT
Catalog page information	Page 191 (CL2-2011)

Product notes

WEEE/RoHS-compliant since:
01/03/2006



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General**

Width (a)	15 mm
Color	transparent
Inflammability class acc. to UL 94	V0
Ambient temperature (operation)	-50 °C ... 80 °C
Components	Silicone-free
Material	PVC