

FEATURES

- Reduced cost and carbon footprint while maintaining quality
- Recyclable and environmentally friendly
- Strong
- Heavy duty with reinforced base, sides and stacking rim
- Index card slot for instant product identification

RS PRO PP Storage Bin Storage Bin, 132mm x 205mm, Black

RS Stock No.: 909-6918



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From RS Pro range of economy plastic storage bins made from robust recycled polypropylene designed for simple and effective small parts organisation and storage in the workplace and in the home. These storage bins are stackable and can be stacked on top of one another to provide both a space saving solution to your storage needs and ease of handling

General Specifications

| Material | PP |
|-------------|---|
| Colour | Black |
| Size | Size 4 |
| Application | Home, Office ,Warehouse ,Laboratory, Hospital, Garage |

Mechanical Specifications

| Volume | 9.1 litres |
|--------------------------------|------------|
| Maximum Container Stack Height | 6mm |
| Maximum Stack Load Capacity | 36kg |
| Weight | 24kg |


| External dimensions | |
|---------------------|-----------------------|
| Dimension | 350mm x 205mm x 132mm |
| Depth | 350mm (Overall) |
| Width | 205mm (Overall) |
| Height | 132mm (Overall) |
| Base Length | 300mm (Overall) |



| Internal dimensions | |
|---------------------|-----------------------|
| Dimension | 330mm x 179mm x 117mm |
| Depth | 330mm |
| Width | 179mm |
| Height | 117mm |
| Base Length | 287mm |


Operation Environment Specifications

| Operating Temperature Range | -15°C to +50°C |
|-----------------------------|----------------|



| | Size 1 | Size 2 | Size 3 | Size 4 | Size 5 | Size 6 | Size 7 |
|---|--------|--------|-----------|--------|--------|--------|--------|
| O/A Length mm (A) | 90 | 165 | 240 | 350 | 350 | 375 | 520 |
| O/A Width mm (B) | 100 | 100 | 150 | 205 | 205 | 420 | 310 |
| O/A Height mm (C) | 50 | 75 | 132 | 132 | 182 | 182 | 200 |
| O/A Base Length mm (D) | 64 | 143 | 200 | 300 | 300 | 310 | 450 |
| Internal Length mm (A) | 80 | 154 | 223 | 330 | 330 | 350 | 470 |
| Internal Width mm (B) | 88 | 88 | 128 | 179 | 177 | 378 | 270 |
| Internal Height mm (C) | 42 | 63 | 120 | 117 | 167 | 164 | 188 |
| Internal Base Length mm (D) | 65 | 131 | 188 | 287 | 287 | 295 | 435 |
| Volume (Litres) | 0.46 | 1.27 | 4.6 | 9.1 | 12.8 | 28.3 | 31.4 |
| Maximum Container stack height | 7 | 5 | 4 | 6 | 4 | 8 | 6 |
| Maximum stack load capacity (kg) See details & image opposite | 12 | 12 | 30 | 36 | 45 | 60 | 42 |





| STACKING CONTAINERS | Size 1 | Size 2 | Size 3 | Size 4 | Size 5 | Size 6 | Size 7 |
|---------------------------------|---------|---------|---------|---------|---------|---------|---------|
| No. Of Containers Per Pack | 20 | 20 | 10 | 10 | 10 | 5 | 5 |
| (Black Repro) RS Stock No. | 9096902 | 9096906 | 9096915 | 9096918 | 9096912 | 9096921 | 9096924 |
| | | | | | | | |
| No. Of Containers Per Pack | - | - | - | - | - | - | 2 |
| (Size 7 Bin Front) RS Stock No. | - | - | - | - | | | 4563432 |