

# Eaton 187862

Catalog Number: 187862

Eaton xEnergy Basic LV systems Low voltage switchgear. Flange plate, IP66, metal, 2xM50/M40 + 2xM40/M32 + 9xM20

General specifications



|  |                |
|--|----------------|
| Product Name                               | Catalog Number |
| Eaton xEnergy Basic installation component | 187862         |
|  | EAN            |
|  | 4015081855476  |
| Product Length/Depth                       | Product Height |
| 5 mm                                       | 140 mm         |
| Product Width                              | Product Weight |
| 230 mm                                     | 0.54 kg        |
| Compliances                                |                |
| RoHS conform                               |                |

## Product specifications

### Features

Pre-stamping

### Number of connector holes

13

### Suitable for nominal thread (PG) - max

50

### Suitable for nominal thread (PG) - min

20

### Degree of protection

Other

### Surface protection

Powder coating

### Shape

Straight

### Material

Steel

### Model

Cable screw gland

### Thread type

Metric

### Thickness

2 mm

### Suitable for cable diameter - max

0 mm

### Suitable for cable diameter - min

0 mm

## Resources

### Brochures

[eaton-xenergy-basic-light-brochure-br014024-en-us.pdf](#)

### Catalogs

[eaton-distribution-boards-xenergy-basic-catalog-ca014010en-en-us.pdf](#)

### Sales notes

[eaton-f3a-flange-flyer-fl019005en-en-us.pdf](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)