Ecoclick Starters

S2 4-22W SER 220-240V WH EUR BOX/20X10

Range of premium-quality glow switch starters for igniting fluorescent lamps with electromagnetic ballast.

Product data

General Information	
System Description	Series

Operating and Electrical	
Power (Nom)	4 22 W
Pulse Voltage (Min)	800 V
Non Reclosure Voltage (Min)	70 V
Voltage (Nom)	220-240 V

System characteristics	
Capacitor	Yes

Mechanical and Housing	
Housing Color	White

Cap-Base Information	2 Pins

Product Data	
Full product code	871150069750931
Order product name	S2 4-22W SER 220-240V WH EUR BOX/20X10
EAN/UPC - Product	8711500697509
Order code	928390720238
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	200
Material Nr. (12NC)	928390720238
Net Weight (Piece)	7.000 g

Ecoclick Starters

Dimensional drawing

F

Product	C (max)	E (max)
S2 4-22W SER 220-240V WH EUR BOX/20X10	40.3 mm	21.5 mm

S2 4-22W SER 220-240V WH EUR

© 2021 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.