

General	Product Name	<b>RIVER 3 (UPS)</b>
	Capacity	245Wh/76800mAh
	Dimension	255 x <b>212</b> x 113 mm 10.0 x <b>8.3</b> x 4.4 inches
	Net. Weight	<b>3.55 kg/7.8 lb</b>
Battery	Battery Chemistry	LFP (LiFePO4)
	Cycle Life	3000 cycles to 80% capacity
Output	AC Output	<b>1 ports, 230V~50Hz, 300W total</b> <b>(Surge 600W, X-Boost 600W)</b>
	USB-A Output	2 ports, 5V=2.4A, 12W Max per port, total 24W
	USB-C Output	<b>1 port, 5/9/12/15V=3A Max, 20V=5A Max, 100W Max</b>
	Car Output	1 port, 12.6V, 10A, 126W Max
	Wireless	<b>✗</b>
Input	AC Recharge	<b>200~240V, 3A Max, 50/60Hz, 300W</b> <b>0~100% in 60 min</b>
	Solar Recharge	11-30V, 8A, 110W Max 0-100% in 2.6 hr (45W input 0-100% in 6.3 hrs) (60W input 0-100% in 4.7 hrs)
	Car Recharge	<b>11~30V, 8A Max, 100W Max</b> 0-100% in 2.8 hr
	Generator Recharge	<b>200~240V, 3A Max, 50/60Hz, 300W</b> <b>0~100% in 60 min</b>
	USB-C Recharge	<b>✗</b>
	Others	UPS
EB		<b>✗</b>
APP		Wi-Fi & Bluetooth
Noise		30db
Waterproof		IP54 only for battery pack, not the whole package
Warranty		2 Years
EB Interface		
Rapid	Capacity	<b>✗</b>
	Dimension	<b>✗</b>
	Net. Weight	<b>✗</b>
	Input/output	<b>✗</b>
Environment Temperature	Optimal Operating Temperature	20°C-30°C (68°F-86°F)
	Charge Temperature	0°C-45°C (32°F-113°F)
	Discharge Temperature	-10°C-45°C (14°F-113°F)
	Storage Temperature	20°C-30°C (68°F-86°F)
Operating Altitude		≤2000 m
What's in the box		RIVER 3 (UPS) AC Charging Cable Car Charging Cable Quick Start Guide and warranty



