

KERN PCJ 600-2M

Precision balance with alibi memory and optional verification

KERN



Category	
Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PCJ

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Weighing capacity [Max]	600 g
Readability [d]	0,01 g
Reproducibility	0,01 g
Linearity	± 0,03 g
USP Minimum weight of sample (k = 2, U = 0.1%)	20 g
Minimum weight [Min]	0,5 g
Resolution	60.000
Tare range	600 g
Adjustment options	Adjusting with internal weight (manual)
Possible calibration points	0 g; 100 g; 200 g; 400 g; 600 g
Automatic adjustment - Standard temperature deviation	2 °C
Automatic adjustment - Standard time interval	8 h
Stabilization time	3 s
Warm-up time	120 min
Eccentric loading at 1/3 [Max]	0,03 g
Default unit	g
Units	kg g gn

	dw tl (Tw) tl (HK) ozt tl (Singap, Malays) ct mo lb oz ffa m
Units (if device is conformity assessed)	kg g
Conformity assessment possible	✓

Display	
Display type	LCD
Display type	LCD
Display backlight	✓
Display screen size	89×30 mm
Display segments	7
Display digit height	21 mm
Languages of the user interface	English Symbol language

Construction	
Dimension housing (W×D×H)	163×245×80 mm
Dimensions completely mounted (W×D×H)	163×245×80 mm
Dimensions weighing surface (W×D)	131×131 mm
Dimensions weighing surface	131×131 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	Stainless steel
Material display housing	Plastics
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Transport safety lock - bolt torque	0,1 Nm

Functions	
PreTare function	✓
Sum memory function	✓
Recipe/summing level	Rez A (Net total)
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual

KERN PCJ 600-2M



Precision balance with alibi memory and optional verification

Underfloor weighing	Hook (included in delivery)
Alibi memory	internal memory
Alibi memory - number of memory spaces	250.000
Function for averaging under unstable weighing conditions	✓
Standby function	✓
Counting function	✓
Counting resolution (laboratory conditions)	30.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	20 mg
Smallest piece weight when piece counting - normal conditions	200 mg
Reference quantity	5, 10, 20, 50, free, Input
IP protection - display	no IP protection
Memory function	✓
Memory - total size	0,016 GB
Auto-off interval(s) in battery mode/rechargeable battery mode	5 min
	2 min
	1 min
	30 min
	60 min
Auto-off interval(s) in mains power mode	30 sec
	off
Tare function	manual (multi)
Number of keys for operation	5

Interface

Interfaces	RS-232 (optional) Bluetooth (optional) Ethernet (optional) USB-Device (optional) KUP WiFi (optional)
EasyTouch (ET) - Compatibility	vollständig

Power Supply

Supplied power supply	Power supply unit
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
	UK
	US
	CH
Plug-in power supply / adapter for countries - optional	EURO UK

	US CH
Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz
Input voltage device / power [Max]	5,9V, 1A
Battery / accumulator type	Li-Ion
Battery	4×1.5 V AA
Battery connection	Plug-in terminals
Battery operating time	20 h
Battery capacity	220 mAh
Battery voltage	3 V
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	48 h
Rechargeable battery charging time	8 h
Rechargeable battery optional	Rchrg. battery optional - intern

Environmental conditions

Ambient temperature [Min]	15 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %

Approval

CE mark	✓
Conformity assessment possible ex works	✓
Accuracy classe	II
Verification scale interval [e]	0,1 g

Services (optional)

Article number for conformity assessment	965-216
Article number for DAkkS calibration	963-127
Article number for certificate of conformity (verification)	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	235×365×175 mm
Net weight	2 kg
Shipping method	Parcel service
Net weight approx.	2,0 kg
Gross weight approx.	2,6 kg
Shipping weight	3 kg


KERN PCJ 600-2M



Precision balance with alibi memory and optional verification

Pictograms

STANDARD



OPTION



FACTORY

