



mecalectro

Small linear solenoid for intensive use – 8.56.AA.62



Stroke: 7 mm

Force at beginning of stroke (FM: 100/25/5%):
1/7/17 N

Force at end of stroke (FM: 100/25/5%):
8/17/35 N

Power Consumption (FM: 100/25/5%):
10/32/12.5 W

Total mass: 150 g

Degree of protection / Energetic class: IP 00 / B

Standard supplies: 24Vcc

Possible supplies: From 12 to 220Vcc

Duty Cycle: Permanent, impulses (100 / 40 / 25 / 15 / 5 %)

Standard: NF C 79300

Examples of applications: Automats, electrical equipment, machinery, security applications.