

310/C8

polywelder with assortment of 7 forms

polywelder with assortment of 7 forms
310/2+310B: Ø 16-20-25
32-40-50-63

 440x270x120 mm -  7,7 kg

	art.		
003100108	310/C8	310/2+310B: Ø 16-20-25 32-40-50-63	

