



Years Warranty*

ANSMANN Powerbank 5000 mAh PB115PD MagSafe

Compact power bank with 5000 mAh capacity for wireless charging via MagSafe; additionally equipped with a USB-C port with Power Delivery (PD)

Features

- 5000 mAh capacity
- Wireless charging with up to 15 W
- Qi-compatible, incl. MagSafe
- additional USB-C output with Power Delivery
- Status and capacity display with 5 LEDs



Article number: 1700-0198
Product content: Powerbank, USB-C cable, manual



Specifications

Nominal voltage	3,7 V			
Ports	1			
Cell chemistry	Lithium polymer			
Nominal capacity	5000 mAh			
Charging currents	Mode	Voltage range	Max. current	Max. power
	Wireless			15,0 W
	Wireless + USB C	5	3,0 A	15,0 W
	USB C	5	3,0 A	15,0 W
	USB C	9	2,2 A	20,0 W
	USB C	12	1,7 A	20,0 W
	PPS	5 - 5,9	3,0 A	17,7 W
	PPS 2	5 - 11	2,0 A	22,0 W
Output ports	Wireless / USB type C			
Input ports	USB type C			
Energy	19,25 Wh			
Color	anthracite			
Operating temperature	0 - 45 °C			
Storage temperature	-20 - 25 °C			
Dimensions	97 × 64 × 11 mm			