

USB 3.1



Product Highlights:

- Stores and transfers content faster with high-speed USB 3.1 performance
- Securely protects files using an advanced security software solution with 256-bit AES encryption
- Protective, retractable cover
- Write speeds up to 10x faster than standard USB 2.0 drives³
- Reliably stores and transfers photos, videos, files, and more
- Compatible with PC and Mac® systems
- USB 3.1 (Gen 1) compatible; backward-compatible with USB 3.0 and 2.0 devices
- Three-year limited warranty

Capacities:

32GB in black, white
(up to 130MB/s read, 25MB/s write)¹

64GB in black, white
(up to 150MB/s read, 60MB/s write)¹

128GB in black, white
(up to 150MB/s read, 60MB/s write)¹

256GB in black, white
(up to 150MB/s read, 60MB/s write)¹



Faster file transfer with USB 3.1 technology

The high-performance Lexar® JumpDrive S80 USB 3.1 Flash Drive allows you to quickly and securely transfer photos, videos, and files with speeds up to 150MB/s read and 60MB/s write¹. Now you can quickly transfer a 3GB 4K movie clip in less than 1 minute, compared to the 4 minutes it takes using a standard USB 2.0 drive². Available in a variety of capacities from 32GB-256GB, this drive also has advanced security software to help give you peace of mind knowing your files are safe. It's also backward-compatible with USB 3.0 and 2.0 devices, providing added versatility. Three-year limited warranty.

Store and transfer content faster. With super-fast speeds up to 150MB/s read and write speeds up to 10x faster than standard USB 2.0 drives³, you can quickly transfer a 3GB 4K movie clip in less than 1 minute, compared to the 4 minutes it takes using a standard USB 2.0 drive². Backwards compatible with USB 3.0 and 2.0 devices.

Securely protect your files. Looking to protect personal information, financial records, or other sensitive files on the go? JumpDrive S80 includes an advanced security software solution with 256-bit AES encryption to help protect your essential files against corruption, loss, and deletion. Easily create a password-protected safe that automatically encrypts data. And for peace of mind, files that are deleted from the safe are securely erased and can't be recovered.

Store it all with a wide range of capacities. JumpDrive S80 comes in a wide range of capacities— 32/64/128/256GB. These options make it easy to find one to suit your needs and store more of your data in one place.

Rigorously tested. All Lexar product designs undergo extensive testing in the Lexar Quality Labs, facilities with more than 1,100 digital devices, to ensure performance, quality, compatibility, and reliability.

For more than 20 years, Lexar has been trusted as a leading global brand of memory solutions. Our award-winning lineup includes memory cards, USB flash drives, card readers, and solid-state drives. With so many options, it's easy to find the right Lexar solution to fit your needs. Lexar products are available worldwide at major retail and e-tail stores. For more information or support, visit www.lexar.com.

¹ Up to 150MB/s read transfer, write speeds lower. Speeds based on internal testing. Actual performance may vary.

² Based on 64GB capacity. 3.2GB video, 4K video.

³ Write speed, up to 10x faster than standard USB 2.0 drives (60MB/s). USB 3.1 Gen 1 or USB 3.0 support required. Based on internal testing; performance may be lower depending upon host device.

Some of the listed storage capacity is used for formatting and other purposes and is not available for data storage. 1GB equals 1 billion bytes. Security safeguards, by their nature, are capable of circumvention. Lexar does not guarantee data will be 100% secure from unauthorized access, alteration, or destruction.

www.lexar.com

©2019 All Rights Reserved. Information, products, specifications, and features are subject to change without notice. Neither Lexar nor Longsys is responsible for omissions or errors in typography or photography. Lexar, the Lexar logo, and all other Lexar trademarks are the property of Longsys Electronics (HK) Co., Ltd. or Shenzhen Longsys Electronics Co., Ltd. All other trademarks are property of their respective owners.