



Main

Range	New Unica
Accessory / separate part category	Installation accessory
Product or component type	Blind cover
Number of modules	1 module
Device presentation	Cover plate
Fixing mode	Clip-in
Colour tint	Anthracite (RAL 7021)

Complementary

Surface finish	Matt
Surface treatment	Painted
Material	Thermoplastic ABS-UV stabilised: centre plate
Depth	22.5 mm
Width	17 mm
Height	45 mm
Type of packing	Flow-pack
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IK degree of protection	IK04
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Circularity Profile	No need of specific recycling operations
Minimum percentage of recycled plastic content	0