
Features

- Stainless-steel pneumatic fitting lockout device.
- Prevents reconnection to compressed air sources.
- Fits male fittings (7 mm – 20.2 mm diameter).
- Solid corrosion-resistant stainless-steel construction.
- Compact and slim design for tight spaces.
- Easy installation and removal.
- Accepts padlocks up to 8 mm shackle diameter.
- Suitable for manufacturing and industrial facilities.

RS PRO Pneumatic Lockout Device - Straight with 9 Holes

RS Stock No.: 0802208



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- ***Prevents Reconnection to Pressurised Air Sources*** *- Specifically engineered to block pneumatic fittings from being reconnected to a compressed air supply during maintenance or servicing.*
- ***Universal Fit for Common Pneumatic Fittings*** *- Designed to fit male pneumatic fittings commonly used in manufacturing facilities.*
- ***Wide Fitting Compatibility Range*** *- Suitable for male fittings with diameters ranging from **7 mm to 20.2 mm**, ensuring versatile application.*
- ***Durable Stainless-Steel Construction*** *- Manufactured from solid stainless-steel sheets for superior strength, durability, and excellent corrosion resistance.*
- ***Compact & Space-Efficient Design*** *- Slim profile dimensions: **35mm (W) × 196mm (H) × 6mm (T)**, ideal for confined industrial environments.*
- ***Simple & Easy Application*** *- Easy to install — place over the male fitting and secure with a padlock.*
- ***Supports Group Lockout*** *- Designed to allow lockout of multiple pneumatic devices simultaneously when required.*
- ***Padlock Compatible*** *- Accepts padlocks with shackle diameters up to **8 mm** for secure isolation.*

General Specifications

Type	Pneumatic Lockout
Material	Stainless Steel
Colour	Metallic Silver
Padlock holes	09
Package	PE-LD

Mechanical Specifications

Dimensions	35mm x 196mm x 6mm
Width	35mm
Height	196mm
Thickness	6mm
Accepted Padlock Shackle Dia.	8mm
Weight	100 Grams

Operation Environment Specifications

Withstand temperature	-40°C to 120°C

