

The Auto Control Easy Tube Load Peristaltic Pump

Model No. AU.UV.EZ

- Variable speed / flow rate
- Brushless motor for 24 hr duty
- Low maintenance
- Manual and analogue control
- 0-10v dc, 4-20mA, 10k Pot
- Easy tube change



Variable speed pump fitted with the Autoclude Easy Tube Load Pump Head,
remote control of speed and stop/start/reverse
using analogue signals or volt free contacts

Features:

- User friendly keypad control
- Two line alpha numeric display
- Manual and analogue control
- Vary flow rate or speed
- Low maintenance brushless motor
- Easy tube load stackable pump head
- Three roller rotor

Technical:

- Flow rates 0.8 to 1312 ml/min
- Speeds from 10 to 250 rpm
- Six tube sizes and five materials
- Remote speed control
- 0-10v dc, 4-20mA or 10K Pot
- Remote Stop/Start/Reverse
- Volt free contacts or 3-36v dc
- 115/230v 50/60 Hz supply

Tube I/D	0.8 mm	1.6 mm	3.2 mm	4.8 mm	6.3 mm	8.0 mm
Flow Rate	0.8 ~ 19 ml/min	2.8 ~ 70 ml/min	11 ~ 270 ml/min	24 ~ 587 ml/min	38 ~ 937 ml/min	53 ~ 1312 ml/min