

RLLLE

ROUND LENS MAGNIFIER



FEATURES:

- Optical-grade glass lens provides 4 diopters of magnification
- For increased magnification, a 4d "Add-X" lens is available
- The 22W circline lamp, along with the satine acrylic lens cover, provides soft, even illumination at the work area
- Spring-loaded arm allows precise adjustability of the magnifier
- Included lens cover protects against dust and scratches
- RLLLE Max has a 43.5in arm and handle for maximum adjustability
- A basic clamp is included and can be used for portable mounting
- No exposed springs eliminates spring corrosion and improves safety
- Lockable pivoting joints allow fixed positioning of magnifier arm

PRODUCT DESCRIPTION:

The RLLLE Series is a conventional approach to magnification and inspection lighting. It provides 4 diopters of magnification and the most rugged construction of any "Ring Magnifier" in the industry. An optional snap-in Add-X lens

increases magnification to 8 diopters. The RLLLE Series magnifier is ideal for inspection applications requiring bright light and strong magnification in a compact, round magnifier. RLLLE includes an energy-efficient electronic ballast and satine acrylic lens for smooth, diffuse light. The high-quality, optical-grade

magnifier is distortion-free and the industrial grade arm with hidden springs and lockable pivoting joints provide precise positioning and adjustment. Arm-mounted switch allows for easy access and one-handed operation. Universal pin mount allows a variety of mounting and installation options.

PRODUCT INFORMATION



RLLLE



ADD-X LENS FOR RLLLE

Voltage:	120V, 50/60Hz
Lamping:	1 x 22W FC8T9 (4100K)
Operation:	Includes switch
Magnification:	4 diopters
Lamp Cover:	Satine acrylic
Lens Diameter:	9.65in (245mm)
Protection Rating:	IP20
Color:	White
Mounting:	Includes table clamp

For mounting options see page 41

DESCRIPTION	PART #
RLLLE-122, 120V, 4d, w/37in reach, w/ C-clamp	138 442 000
RLLLE-122, 120V, 4d+12d, w/37in reach, w/ C-clamp	138 442 001
RLLLE-122 Max, 120V, 4d, w/43.5in reach, w/ C-clamp	138 442 005
RLLLE-122 Max, 120V, 4d+12d, w/43.5in reach, w/ C-clamp	138 442 009
Replacement Lamp, 22W circline, 4100K	450 022 010
Add-X Lens, 4d (2X)	190 054 019