

Model No. 410TEAL

Teal Zenex™ Thermoplastic Safety Padlock, 1-1/2in (38mm) Wide with 1-1/2in (38mm) Tall Shackle

Best Used For:

LOCKOUT/ TAGOUT Lockout Tagout

LOCKOUT/ TAGOUT Safety Lockout/Tagout

Overview & Features

Product Features


- 410 Thermoplastic Safety Padlock
- 1-1/2in (38mm) wide, 1-3/4in (44mm) tall Thermoplastic teal body, shackle with 1-1/2in (38mm) clearance
- Designed exclusively for lockout tagout applications
- Durable, lightweight, non-conductive Thermoplastic lock body
- Customize on-site with permanent, write-on labels
- Compliance with "One Employee, One Lock, One Key" directive
- High security, reserved-for-safety cylinder
- Key retaining - ensures that padlock is not left unlocked
- Keyed different, 6-pin tumbler with over 40,000 available key changes cylinder, Shelf Pack Qty 6, Master Carton Qty 36

Product Details

The Master Lock No. 410TEAL Zenex™ Thermoplastic Safety Padlock features a 1-1/2in (38mm) wide plastic teal body and a 1-1/2in (38mm) tall, 1/4in (6mm) diameter metal shackle. Designed exclusively for Lockout/Tagout applications, the durable, lightweight, non-conductive lock body is easy to carry and padlock features high security, reserved-for-safety cylinder with key retaining, to ensure padlock is not left unlocked.

Product Specifications

Product Number	410TEAL
Body Width	38mm
Shackle Dimensions	A: 6 mm B: 38 mm C: 20 mm
Colour	Teal
Description	Keyed Different, Commercial Boxed Packaging
Shelf Pack Qty	6
Master Carton Qty	36



Master Lock Europe S.A.S.
10 avenue de l'arche - Le Colisée Gardens, bâtiment A - 92 400 Courbevoie - La Défense - France
O:+33-1-41437200 | F:+33-1-41437204
www.masterlock.eu